




# VISIOCAP

In-line inspection system to detect minimum capping defect.



- ✔ It does not require maintenance.
- ✔ Long life system and fast amortization.
- ✔ Automatic height adjustment of the inspection bridge.
- ✔ Intuitive user interface.
- ✔ Quick and easy format changes.
- ✔ Parameters and tolerances setting for each format.
- ✔ Visual adjustment of control parameters.
- ✔ Real time production statistics.
- ✔ Remote control via internet and remote diagnosis.
- ✔ Rejection signal management. E2M offers a wide range of defective bottle rejection systems. Also for carafes.
- ✔ Rejection signal management. E2M offers a wide range of defective bottle rejection systems. Also for carafes.



ORIENTING

INSPECTING

REJECTING

ANY KIND OF EMPTY OR FULL BOTTLES AND CONTAINERS

# VISIOCAP

In-line inspection system to detect minimum capping defect.



**VELOCITY**  
72.000 CNT/H



**GAP**  
1 · Ø

## FEATURES

- Up to 3 CMOS 1.3 Mp B / W cameras.
- LED lighting system.
- High performance production, up to 90,000 u / h depending on the inspections to be performed.
- IP67 protection stainless steel enclosure for cameras.
- Intel latest generation processor.
- Windows 10 based computer system and interface.
- 17" TFT touch screen for communication with the operator.
- Keyboard with mouse.
- USB, Ethernet
- Container position control by sensor and encoder.
- Possibility of implementing an upper zenithal chamber.

## MONITORING:

### OPERATING MONITORING OF:

- Capper heads.
- Filler valves

### DETECTION OF FALLEN BOTTLES OR BLOWN BOTTLES

## ACTIVITY SECTORS

- Bottled mineral water.
- Wine.
- Sparkling wine and champagne.
- Spirits.

## KEY SYSTEM IN HAND FOR INSPECTION OF:



Absence of the cap



Cocked cap



Threading degree (insertion depth)



Broken or damaged seal ring



Distance between neck ring and cap (6 observation points)



Fill level (depending on fill height)

- Beers.
- Oils and vinegars.
- Pharmacy and cosmetics.
- Juices and soft drinks.



**Estudis Electro-Mecànics, S.L.**  
Pau Vila i Dinarés, 4-10  
08192 Sant Quirze del Vallès, Barcelona, Spain  
T. +34 93 720 85 40 F. +34 93 720 85 25  
[www.e2m.es](http://www.e2m.es)



OUR NETWORKS



GET UPDATE!

E2m offers customized solutions to meet specific requirements of each customer.  
Technical specifications updated on the website.